





Massecuite flow. Under control.

BMA have developed an improved sight glass for visual monitoring of the massecuite entering a centrifugal. It consists of a hard-wearing transparent plastic tube clamped between two stainless steel flanges. The upgrade kit is available in sizes DN150 and DN200.



Benefits

- Better control of the massecuite flow
- Secure design of the sight glass clamping
- Easy to install
- Reduced maintenance costs

The upgrade kit comprises

- Massecuite feed duct
- Rubber compensator
- Sight glass
- Complete with flanges and stud bolts

Installation is supervised by a centrifugal specialist from BMA.

© BMA

Postfach 32 25 38022 Braunschweig Am Alten Bahnhof 5 38122 Braunschweig

Telefon +49 531 804-0 Fax +49 531 804-216 assistance@bma-de.com